

SM4641 DATA SHEET

7/16 DIN Male (Plug) to HN Female (Jack) Adapter, Nickel Plated Brass Body, High Temp, 1.5 VSWR

7/16 DIN male to HN female adapter part number SM4641 from Fairview Microwave is in-stock and ships same day. This Fairview 7/16 DIN to HN adapter has a male to female gender configuration. SM4641 7/16 DIN male to HN female adapter operates to 4 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.5:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		4	GHz
VSWR			1.5:1	
Operating Voltage (AC)			1,500	Vrms
DWV (AC)			4,000	Vrms
Insulation Resistance	5,000			MOhms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 1	1 to 4				GHz
VSWR, Max	1.2:1	1.5:1				

Electrical Specification Notes: Value at 25° C, sea level

Mechanical Specifications

-	-	
•	17	0
9	14	C

0.20	
Length	1.72 in [43.69 mm]
Width	1.25 in [31.75 mm]
Height	1.25 in [31.75 mm]
Weight	0.26 lbs [117.93 g]

l Male HN Female
ard Standard
-348 MIL-STD-348
500
nch
s max



Configuration:

- 7/16 DIN Male Connector 1
- HN Female Connector 2
- 50 Ohm
- Straight Body Geometry

Features:

- VSWR of 1.5:1 max up to 4 GHz
- 7/16 DIN interface meets MIL-STD-348
- HN interface meets MIL-STD-348
- Gold Plated Beryllium Copper Contact

Applications:

- Enables Between Series Connections
- General Purpose Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 2
Туре	7/16 DIN Male	HN Female
Contact Material	Beryllium Copper	r Beryllium Copper
Contact Plating	Gold	Gold
Insulation Material	PTFE	PTFE
Outer Contact Material		Brass
Outer Contact Plating		Nickel
Body Material	Brass	Brass
Body Plating	Nickel	Nickel
Gasket Material	Rubber	Rubber
Coupling Nut Material	Brass	
Coupling Nut Plating	Nickel	

Environmental Specifications

Temperature

Operating Range


-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data








7/16 DIN Male (Plug) to HN Female (Jack) Adapter, Nickel Plated Brass Body, High Temp, 1.5 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 7/16 DIN Male (Plug) to HN Female (Jack) Adapter, Nickel Plated Brass Body, High Temp, 1.5 VSWR SM4641

URL: https://www.fairviewmicrowave.com/7-16-male-hn-female-adapter-sm4641-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





