

Precision SMA Female (Jack) to N Female (Jack) Adapter, 1.15 VSWR, High Temp

SM4236

Configuration

- SMA Female Connector 1
- · N Female Connector 2
- · 50 Ohms Impedance

Features

- VSWR of 1.15:1 max up to 18 GHz
- Contact plating according to MIL-G-45204

Applications

- · Enables Between Series Connections
- · General Purpose Test

- · Precision Design
- Straight Body Geometry
- · Gold over Nickel Plated Beryllium Copper Contact
- Precision Test & Measurement

Description

SMA female to type N female adapter part number SM4236 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to type N adapter has a female to female gender configuration in a precision design. SM4236 SMA female to type N female adapter operates to 18 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.15:1 maximum. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		18	GHz
Impedance		50		Ohms
VSWR	-		1.15:1	

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Size

 Length
 1.24 in [31.37 mm]

 Width
 0.62 in [15.75 mm]

 Height
 0.62 in [15.75 mm]

 Weight
 0.06 lbs [28.03 g]

Description	Connector 1	Connector 2	
Polarity	Standard	Standard	
Mating Cycles, Min	500	500	



Precision SMA Female (Jack) to N Female (Jack) Adapter, 1.15 VSWR, High Temp



SM4236

Material Specifications

	Connector 1			Connector 2	
Description	Material	Plating	Material	Plating	
Туре	SMA Female		N Female		
Contact	Beryllium Copper	Gold over Nickel	Beryllium Copper	Gold over Nickel	
		MIL-G-45204		MIL-G-45204	
Insulation	PTFE		PTFE		
Outer Conductor	Passivated Stainless Steel	ASTM A380	Passivated Stainless Steel	ASTM A380	

Environmental Specifications

Temperature

Operating Range Vibration Salt Spray -65 to +165 °C


MIL-STD 202, Method 204, Condition D (20 G's)

MIL-STD 202, Method 101, Condition B, 5% salt solution

Compliance Certifications (see product page for current document)

Plotted and Other Data

Typical Performance Data





Precision SMA Female (Jack) to N Female (Jack) Adapter, 1.15 VSWR, High Temp



SM4236

Precision SMA Female (Jack) to N Female (Jack) Adapter, 1.15 VSWR, High Temp from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Precision SMA Female (Jack) to N Female (Jack) Adapter, 1.15 VSWR, High Temp SM4236

URL: https://www.fairviewmicrowave.com/sma-female-n-female-adapter-sm4236-p.aspx

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

