

SMA-SMA SWEPT ADAPTERS

SM5280, SM5285, SM5290, SM5295

SPECIFICATIONS

ELECTRICAL


50 OHMS
 VSWR 1.40:1 MAX @ 18 GHZ
 FREQUENCY: 0-18 GHZ

MECHANICAL


500 CYCLES MIN
 INTERFACE: MIL-STD-348A

MATERIALS


BODY PASSIVATED STAINLESS STEEL
 CONTACTS BeCu(f), BRASS(m)
 CONTACT PLATING: Au MIL-G-45204
 DIELECTRIC: TEFLON
 OP TEMP -55°-125°C
 TORQUE: 7.5-8 in-IBS
 ROHS COMPLIANT




SM5290



SM5285




SM5280



SM5295

MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA-SMA SWEPT ADAPTERS

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SM5280 - SM5295	G
SCALE		SHEET	