

SMA-TNC 18GHZ ADAPTERS

SM4735, SM4736, SM4737, SM4738

SPECIFICATIONS



ELECTRICAL

FREQUENCY: 0-18 GHZ
 IMPEDANCE: 50 OHMS
 VSWR: 1.25:1 MAX


MECHANICAL

MATERIALS BODY PASS STAINLESS STEEL
 FEMALE CONTACTS BeCu
 CONTACT PLATING: Au MIL-G-45204
 INSULATOR: TEFLON
 DURABILITY: 500 CYCLES MIN
 INTERFACE: MIL-STD-348A
 OPERATING TEMPERATURE; -55 to 100°C
 SMA COUPLING NUT TORQUE 7-9 IN-LBS
 ROHS COMPLIANT


MEASUREMENTS BELOW ARE TYPICAL




SM4735



SM4737



SM4736



SM4738

ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM			
TITLE			
SMA-TNC 18GHZ ADAPTERS			
SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SM4735 - SM4738	A
SCALE		SHEET	