



Precision SMA Female to SMP Male Smooth Bore CM 2 Hole Flange Adapter

Precision SMA female to SMP male smooth bore CM 2 hole flange adapter part number SM8837 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMP adapter has a female to male gender configuration in a precision design. SM8837 SMA female to SMP male adapter operates to 26.5 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. Our RF SMA to SMP 2 hole flange adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		26.5	GHz
VSWR			1.2:1	

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Size		
Length		
Width		
Weight		

0.78 in [19.81 mm] 0.63 in [16 mm] 0.0115 lbs [5.22 g]

Description	Connector 1	Connector 2
Туре	SMA Female	SMP Male
Connection Method		Smooth Bore CM
Polarity	Standard	Standard
Interface Specification	MIL-STD-348	
Mating Cycles	500	
-		



Configuration:

- SMA Female Connector 1
- Smooth Bore CM SMP Male Connector 2
- 50 Ohm
- Precision Design
- Straight Body Geometry
- 2 Hole Flange Mount Method

Features:

- VSWR of 1.2:1 max up to 26.5 GHz
- SMA interface meets MIL-STD-348
- Contact plating according to MIL-G-45204
- Gold Plated Beryllium Copper Contact

Applications:

- Enables Between Series Connections
- General Purpose Test
- Rack Mounted Equipment
- Precision Test & Measurement

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 2
Туре	SMA Female	SMP Male
Contact Material	Beryllium Copper	Beryllium Copper
Contact Plating	Gold	Gold
Contact Plating Spec.	MIL-G-45204	MIL-G-45204
Insulation Material	PTFE	PTFE
Outer Contact Material	Passivated Stainless Stee	l
Outer Contact Plating Spec.	AMS-QQ-P-35	
Body Material		Passivated Stainless Steel
Body Plating Spec.		AMS-QQ-P-35

Environmental Specifications

Temperature

Operating Range


-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







Precision SMA Female to SMP Male Smooth Bore CM 2 Hole Flange Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: Precision SMA Female to SMP Male Smooth Bore CM 2 Hole Flange Adapter SM8837

URL: https://www.fairviewmicrowave.com/sma-female-smp-male-smooth-bore-2-hole-flange-adapter-sm8837-p.aspx









NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.

2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.

3. DIMENSIONS ARE IN INCHES [mm]. Fairview Microwave DWG NO CAGE CODE SM8837 3FKR5 Precision SMA Female to SMP Male Smooth Bore CM 2 Hole Flange Adapter CAD FILE 05/01/18 SHEET 1 OF 1 SCALE N/A SIZE A 7361