

# SMA-TNC 11GHZ PRECISION ADAPTERS

SM4761, SM4764, SM4766, SM4773

## SPECIFICATIONS

### ELECTRICAL:


FREQUENCY: 0-11 GHZ  
 IMPEDANCE: 50 OHMS  
 VSWR: 1.20:1 MAX

### MECHANICAL:


MATERIALS BODY SMA PASS. STAINLESS STEEL  
 MATERIALS BODY TNC NICKEL PLATED BRASS  
 FEMALE CONTACTS BeCu  
 CONTACT PLATING: Au PER MIL-G-45204

OPERATING TEMPERATURE;  
 -55 to 100°C


ROHS COMPLIANT




SM4761



SM4773




SM4766



SM4764

MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

**FAIRVIEW MICROWAVE INC.**

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**SMA-TNC 11GHZ PRECISION ADAPTERS**

SIZE <b>A</b>	CAGE CODE <b>3FKR5</b>	DWG NO <b>SM4761, 4764, 4766, 4773</b>	REV <b>A</b>
------------------	---------------------------	---	-----------------

SCALE

SHEET