

WR-62 Waveguide Section 12 Inch Length Straight Using UG-419/U Flange With a 12.4 GHz to 18 GHz Frequency Range in Instrumentation Grade

Fairview Microwave carries a wide variety of waveguide sections ranging from WR-12 to WR-137. These waveguide sections include grooved and non-grooved designs. Standard lengths of our waveguide sections include 3", 6", 9", and 12" (custom lengths available upon request). For ease of identification, our commercial grade waveguide sections are painted grey while our instrumentation grade waveguide sections are gold plated. Our instrumentation grade waveguide sections were designed with precision tolerances as tight as ± 0.001 " and were constructed of a high grade oxygen free copper to ensure repeatable RF performance.

Electrical Specifications*

Description	Min	Тур	Мах	Units
Frequency Range	12.4		18	GHz
VSWR			1.06:1	
Insertion Loss			0.1 [0.33]	dB/ft [dB/m]

WR-62

* Values at 25°C, sea level

Mechanical Specifications

Waveguide Size Waveguide Design Section Length

Flange 1

Interface Material Plating

Waveguide

Interface Material Plating

Flange 2

Interface Material Plating Instrumentation Grade 12 in [304.8 mm]

UG-419/U Oxygen Free Hard Copper Hard Gold over Copper Flash

WR-62 Oxygen Free Hard Copper Hard Gold over Copper Flash

UG-419/U Oxygen Free Hard Copper Hard Gold over Copper Flash

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:

• Values at 25 °C, sea level



SMF-62S001-12

DATA SHEET

Features:


- Commercial grade and instrumentation grade sections and bends covering frequency ranges from 5.8 GHz to 90 GHz
- Wide variety of flange types, including grooved and non-grooved designs
- Custom lengths available
 upon request
- Precision waveguide mechanical tolerances as tight as ±0.001"
- Comprehensive waveguide offering also includes Bends, Filters, Terminations, and Waveguide to Coaxial Adapters

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Typical Performance Data







File File	Trace/Chan	Response	Marker/Analysis	Stimulus						_ & ×
Chan	nel 1 SM	F-62S00	1-12 VSWR		Sto	p Frequenc	y 18.00	0000000 GHz	*	Display Items
	Tr 1 S11 SV	VR 1.000U/	1.00U							Display reems
11.00										Tible
10.00										Title
10.00										Trace Status
9.00										ON off
8.00										Freq, Stim ON off
									1	
7.00							-		_	Marker
										Display
6.00									_	Grid
										SOLID dotted
5.00				-			_		-1	
4.00									-1	
									- 11	
3.00									٦ŀ	
									- 11	Return
2.00										
1.00	Ch 1 Avg =	50							- 11	Favorites
P								ravontes		
Cont.	CH 1: S11		2-Port	Avg=50	Smooth=	4.48%				LCL

WR-62 Waveguide Section 12 Inch Length Straight Using UG-419/U Flange With a 12.4 GHz to 18 GHz Frequency Range in Instrumentation Grade from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: WR-62 Waveguide Section 12 Inch Length Straight Using UG-419/U Flange With a 12.4 GHz to 18 GHz Frequency Range in Instrumentation Grade SMF-62S001-12


URL: http://www.fairviewmicrowave.com/wr-62-waveguide-section-ug-419-flange-12.4-18-ghz-smf-62s001-12-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689