

SM8723 DATA SHEET

RA TNC Male to TNC Female Adapter

RA TNC male to TNC female adapter part number SM8723 from Fairview Microwave is in-stock and ships same day. This Fairview TNC to TNC adapter has a male to female gender configuration. SM8723 TNC male to TNC female adapter operates to 2 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.5:1 maximum. This right angle TNC adapter allows for easier connections in tight spaces.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		2	GHz
VSWR			1.5:1	
Operating Voltage (AC)			500	Vrms

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

Size Length Height	1.14 in [28.96 mm] 1.08 in [27.43 mm]
Weight	0.057 lbs [25.85 g]

Description	Connector 1	Connector 2	
Туре	TNC Male	TNC Female	
Polarity	Standard	Standard	
Mating Cycles	500	500	



Configuration:

- TNC Male Connector 1
- TNC Female Connector 2
- 50 Ohm
- Right Angle Body Geometry

Features:

- VSWR of 1.5:1 max up to 2 GHz
- · Gold Plated Brass Contact

Applications:

General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 2		
Туре	TNC Male	TNC Female		
Contact Material	Brass	Brass		
Contact Plating	Gold	Gold		
Insulation Material	PTFE	PTFE		
Outer Contact Material		Brass		
Outer Contact Plating		Nickel		
Outer Conductor Contact Spe	ec.	100 µin minimum		
Body Material	Brass			
Body Plating	Nickel			
Body Plating Spec.	100 μin minimum			

Environmental Specifications

Temperature

Operating Range


-20 to +80 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







RA TNC Male to TNC Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order


For additional information on this product, please click the following link: RA TNC Male to TNC Female Adapter SM8723

URL: https://www.fairviewmicrowave.com/ra-tnc-male-tnc-female-adapter-sm8723-p.aspx

				ave reserves the r					
				w Microwave does					
				y particular purpos	se, and Fair	view Mi	crowave do	es not assume a	ny liability
arising out	t of the use of	any part or do	cument	tation.					







STANDARD TOLERANCES

X ±0.2 XX ±0.1 XXX ±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	ISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. DNS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. : IN INCHES [mm].					
RA TNC Male to TNC Female Adapter	DWG NO CAGE CODE				3FKR5	
	CAD FILE 091916	SHEET	SCALI	E N/A	SIZE A	41742