


# POWER DIVIDER N 800-2500MHZ 2-WAY

SMP8710

## SPECIFICATIONS

### ELECTRICAL

FREQUENCY: 800-2500 MHZ  
ISOLATION: 0 DB  
POWER: 200W AVG  
IMPEDANCE: 50 OHMS  
VSWR: 1.25:1 MAX , ALL PORTS  
AMPLITUDE BALANCE: 0.15DB  
LOSS: 3.2 DB MAX (3+.2)




### MECHANICAL

MATERIALS BODY: PASSIVATED ALUMINUM  
CONNECTORS: N-FEMALE, NICKEL PLATING  
TEMP RANGE: -30 TO +60 DEG C  
WEIGHT: 10 oz

ROHS COMPLIANT

MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

## FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

### POWER DIVIDER N 800-2500MHZ 2-WAY

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SMP8710	A
SCALE		SHEET	