

POWER DIVIDER N 698-2700MHZ 4-WAY

SMP8756

SPECIFICATIONS


ELECTRICAL

FREQUENCY: 698-2700 MHZ
 ISOLATION: 20 DB MIN
 POWER: 10 W AVG
 IMPEDANCE: 50 OHMS
 VSWR: 1.25:1 MAX , ALL PORTS
 AMPLITUDE BALANCE: 0.3dB
 INSERTION LOSS: 0.6dB MAX
 SPLIT LOSS: 6dB
 TEMP. RANGE: -30° to +60°


MECHANICAL

MATERIALS BODY: PASSIVATED ALUMINUM
 CONNECTORS: N-FEMALE, TRIPLATE

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(mm) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

POWER DIVIDER N 698-2700MHZ 4-WAY

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SMP8756	--
SCALE	SHEET		