

## SPO-375 Low Loss Corrugated Coax Cable Black PE Jacket Superflexible Outdoor Rated

### Times Microwave Systems Coax Cable Specification

SPO-375 low loss outdoor rated coax cable by Times Microwave is part of our full line of RF components available for same-day shipping. The SPO-375 coaxial cable features a low loss dielectric with an 83% velocity of propagation (VoP), BCCAL center conductor and a helically corrugated, copper outer conductor. These features combine to make the Times Microwave SPO-375 a super flexible, low PIM coax cable that is well suited for use as an antenna jumper cable, Distributed Antenna Systems (DAS), small cell, and other outdoor applications. The tough, black polyethylene jacket provides moisture and UV protection and is suitable for outdoor use.

Our datasheet specifications and drawing with dimensions for Times Microwave SPO-375 coax cable are shown below in this PDF. Whether the need is to provide a low PIM jumper connection, low PIM feeder cable or simply create a custom cable assembly configuration, Fairview Microwave has the right SPO-375 cable assembly for the job. See our web site to find the right connector cable combination for your application.



### Configuration:

- Low Loss Corrugated Cable
- 1 Shield(s)

### Features:

- PIM < -160 dBc
- Lightweight and Super Flexible
- Low Loss Dielectric 83% VoP
- Shielding > 100 dB
- Durable Black Polyethylene Outer Jacket
- Outdoor Rated

### Applications:

- Distributed Antenna Systems (DAS)
- Antenna Installations
- Small Cell
- Outdoor Applications
- Commination Tower Install

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
Velocity of Propagation		83		%
Passive Intermodulation			-158	dBc
Nominal Capacitance		24		pF/ft
		[78.74]		[pF/m]

### Performance by Frequency Band

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2	6		GHz
Attenuation, Typ	2.96	4.33	6.23	11.62		dB/100ft
	9.71	14.21	20.44	38.12		dB/100m
Power In (CW), Max	970	740	510	220		Watts

### Mechanical Specifications

Diameter	0.43 in [10.92 mm]
Weight	0.132 lbs/ft [0.2 Kg/m]
Min. Bend Radius (Installation)	1.75 in [44.45 mm]

### Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper Clad Aluminum, 1 Strands	0.11 in [2.79 mm]
Conductor Type	Solid	
Dielectric	Foam PE	0.27 in [6.86 mm]

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

Outer Conductor	Copper Corrugated	0.38 in [9.65 mm]
Jacket	PE, Black	0.43 in [10.92 mm]

**Environmental Specifications**

**Temperature**

Operating Range -40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**


Notes:

SPO-375 Low Loss Corrugated Coax Cable Black PE Jacket Superflexible Outdoor Rated from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SPO-375 Low Loss Corrugated Coax Cable Black PE Jacket Superflexible Outdoor Rated SPO-375](#)

URL: <https://www.fairviewmicrowave.com/spo375-low-loss-corrugated-coax-cable-pe-jacket-spo-375-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.01
.XXX	±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

<p><b>Fairview Microwave</b> RF COMPONENTS ON DEMAND. <i>Done!</i></p>	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].							
	TITLE SPO-375 Low Loss Corrugated Coax Cable Black PE Jacket Superflexible Outdoor Rated			DWG NO SPO-375		CAGE CODE 3FKR5		
	CAD FILE	03/07/19	SHEET	1 OF 1	SCALE	N/A	SIZE	A