

0 to 30 dB WR-15 Waveguide Continuously Variable Attenuator From 50 GHz To 75 GHz Dial And UG-385/U Flange

Electrical Specifications*

Description	Min	Typ	Max	Units
Frequency Range	50		75	GHz
Impedance		50		Ohms
Typical Attenuation Value	0		30	dB
Insertion Loss			0.8	dB

Values at 25°C, sea level

Mechanical Specifications

Flange 1

Interface UG-385/U
 Material Copper
 Plating Gold
 Color Gold

Waveguide

Interface WR-15
 Material Copper
 Plating Gold
 Color Gold

Flange 2

Interface UG-385/U
 Material Copper
 Plating Gold
 Color Gold

Size

Length 2.5 in [[63.5 mm]]
 Width 0.75 in [[19.05 mm]]
 Height 2.165 in [[54.99 mm]]



Features:

- Design: Continuously Variable Attenuator
- Waveguide: WR-15
- Flange: UG-385/U
- Body Material and Plating: Copper, Gold

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant Yes


Plotted and Other Data

Notes:

- Values at 25 °C, sea level

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data




0 to 30 dB WR-15 Waveguide Continuously Variable Attenuator From 50 GHz To 75 GHz Dial And UG-385/U Flange from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [0 to 30 dB WR-15 Waveguide Continuously Variable Attenuator From 50 GHz To 75 GHz Dial And UG-385/U Flange SMW15AT001-30](#)

URL: <http://www.fairviewmicrowave.com/30-db-wr-15-waveguide-step-attenuator-75-ghz-smw15at001-30-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN: [mm]
 TOLERANCES ARE: inches
 .XX ± .02 [±.51]
 .XX ± .005 [±.13]

* THESE DIMENSIONS AND TOLERANCES
 SUPERSEDE NOTE #1 ON TITLE BLOCK.

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE 0 to 30 dB WR-15 Waveguide Continuously Variable Attenuator From 50 GHz To 75 GHz Dial And UG-385/U Flange		DWG NO SMW15AT001-30		CAGE CODE 3FKR5	
CAD FILE	032315	SHEET	SCALE	N/A	SIZE A 200