



SMC Plug (Male) Termination (Load) 1 Watts To 10 GHz, 1.3 VSWR

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		10	GHz
Impedance		50		Ohms
VSWR			1.3:1	
Input Power (CW)			1	Watt



Mechanical Specifications

 Size

 Length
 0.504 in [12.8 mm]

 Width
 0.236 in [5.99 mm]

 Weight
 0.005 lbs [2.27 g]

Configuration

Connector SMC Plug

Material Specifications

Description	Material	Plating	
Connector 1 Contact	Beryllium Copper	Gold	
Insulation	PTFE		
Body	Brass	Gold	

Environmental Specifications

Temperature

Operating Range -45 to +120 deg C

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

SMC Plug (Male) Termination (Load) 1 Watts To 10 GHz, 1.3 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: SMC Plug (Male) Termination (Load) 1 Watts To 10 GHz, 1.3 VSWR ST3923

URL: https://www.fairviewmicrowave.com/rf-load-1-watts-10-ghz-smc-plug-st3923-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





