

BNC Male (Plug) Termination (Load) 2 Watts to 4 GHz with Chain, Tri-Metal Plated Brass, 1.15 VSWR, 1 KWatts Peak Power

RF termination (also called RF load or dummy load) ST3B-C from Fairview Microwave operates from DC to 4 GHz and handles up to 2 Watts (CW). This BNC termination (or load) has a male gender. ST3B-C BNC load termination offers 1.15:1 max VSWR.

RF terminations / loads are critical passive components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can reduce the signal integrity and can potentially damage the device. By terminating an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These radio frequency termination components are commonly used to terminate devices such as couplers, circulators, and switches. Loads / terminations are also widely used in measurement systems to ensure accurate results. Fairview offers a large selection of in-stock RF, microwave and millimeter wave terminations up to 65 GHz with great performance over the entire operating range and with power handling capabilities up to 800 Watts (CW).



Features:

- DC to 4 GHz Frequency Range
- VSWR 1.15:1 Max
- Max Power 2 Watts (CW)
- BNC Male Coaxial Interface
- Includes Beaded Chain

Applications:

- Wireless
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communication

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		4	GHz
Impedance		50		Ohms
VSWR			1.15:1	
Input Power (CW) derated linearly to 1W at +125°C			2	Watts
Input Power (Peak) 50 µsec duration			1	kWatts

Mechanical Specifications

Size	
Length	1.14 in [28.96 mm]
Width	0.58 in [14.73 mm]
Weight	0.046 lbs [20.87 g]

Configuration

Connector	BNC Male
-----------	----------

Material Specifications

Description	Material	Plating
Insulation	PTFE	
Body	Brass	Tri-Metal
Coupling Nut	Brass	Tri-Metal
Housing	Brass	Tri-Metal
Chain	Brass	Nickel

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -55 to 125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data


Notes:

BNC Male (Plug) Termination (Load) 2 Watts to 4 GHz with Chain, Tri-Metal Plated Brass, 1.15 VSWR, 1 KWatts Peak Power from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [BNC Male \(Plug\) Termination \(Load\) 2 Watts to 4 GHz with Chain, Tri-Metal Plated Brass, 1.15 VSWR, 1 KWatts Peak Power ST3B-C](#)

URL: <https://www.fairviewmicrowave.com/rf-load-2-watts-4-ghz-chain-bnc-male-st3b-c-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
DECIMAL	
.XX	±0.20
.XXX	±0.10

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		DWG NO		CAGE CODE	
TITLE BNC Male (Plug) Termination (Load) 2 Watts to 4 GHz with Chain, Tri-Metal Plated Brass, 1.15 VSWR, 1 KWatts Peak Power		ST3B-C		3FKR5	
		CAD FILE	062416	SHEET	SCALE
				SIZE	A
				3045	