

ST6011 DATA SHEET

RF Load 1 Watts To 6 GHz Gold Plated Beryllium Copper MCX Plug

RF termination (also called RF load or dummy load) ST6011 from Fairview Microwave operates from DC to 6 GHz and handles up to 1 Watt (CW). This MCX termination (or load) has a plug connection type. ST6011 MCX load termination offers 1.3:1 max VSWR.

RF terminations / loads are critical passive components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can reduce the signal integrity and can potentially damage the device. By terminating an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These radio frequency termination components are commonly used to terminate devices such as couplers, circulators, and switches. Loads / terminations are also widely used in measurement systems to ensure accurate results. Fairview offers a large selection of in-stock RF, microwave and millimeter wave terminations up to 65 GHz with great performance over the entire operating range and with power handling capabilities up to 800 Watts (CW).

Electrical Specifications

Description	Min	Тур	Мах	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
VSWR			1.3:1	
Input Power (CW)			1	Watts

Mechanical Specifications

Size	
Length	0.49 in [12.45 mm]
Width	0.2 in [5.08 mm]
Weight	0.0022 lbs [1 g]
Configuration Connector	MCX Plug

Material Specifications

Description	Material	Plating	
Connector 1 Contact	Brass	Gold	
Insulation	PTFE		
Body	Beryllium Copper	Gold	
Housing	Beryllium Copper	Gold	

Environmental Specifications Temperature

Operating Range

-45 to +120 deg C



Features:

- DC to 6 GHz Frequency Range
- VSWR 1.3:1 Max
- Max Power 1 Watt (CW)
- MCX Plug Coaxial Interface

Applications:

- Wireless
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communication

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant REACH Compliant Yes 12/17/2015

Plotted and Other Data


Notes:

RF Load 1 Watts To 6 GHz Gold Plated Beryllium Copper MCX Plug from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: RF Load 1 Watts To 6 GHz Gold Plated Beryllium Copper MCX Plug ST6011

URL: https://www.fairviewmicrowave.com/rf-load-1-watts-6-ghz-mcx-plug-st6011-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







STANDARD TOLERANCES DECIMAL .XX ±0.20 .XXX ±0.10

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
π⊓LE RF Load 1 Watts To 6 GHz Gold Plated Beryllium Copper MCX Plug	DWG NO ST6011		C	CAGE CODE 3FKR5		
	CAD FILE 061516	SHEET	SCALE N	N/A	SIZE A	3045

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689