

## WR-284 Standard Gain Horn Antenna Operating From 2.6 GHz to 3.95 GHz, 20 dBi Nominal Gain, Type N Female Input Connector, ProLine

The Fairview Microwave FM9863B/NF-20 Proline series standard gain horn antenna (also known as waveguide horn) is part of our huge selection of waveguide antennas. This Fairview Microwave standard gain horn antenna is manufactured with a WR-284 input and a Type N waveguide to coaxial transition adapter. Our standard gain horn antenna, WR-284, has a 20 dBi nominal gain. This WR-284 standard gain horn from Fairview Microwave has a female Type N waveguide to coax transition adapter. The 20 dBi Fairview Microwave WR-284 horn antenna operates from 2.6 GHz to 3.95 GHz. Fairview Microwave's Type N female WR-284 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and rectangular input. It is part of over 40,000 RF, microwave and millimeter wave components available at Fairview Microwave. Waveguide standard gain horn antennas, such as the FM9863B/NF-20, are used in a wide variety of applications due to their high power handling capability, low loss, high directivity, and near constant electrical performance. The WR-284 FM9863B/NF-20 waveguide horn is US made and TAA compliant. Our WR-284 standard gain horn Proline antennas with Type N female interface can ship same day to anywhere in the world.



### Features:

- WR-284 Rectangular Waveguide Interface
- 2.6 GHz to 3.95 GHz
- 20 dBi Nominal Gain
- Type N Female Connector

### Applications:

- Antenna Measurements
- Wireless Communication
- Laboratory Use
- Microwave Radio System

### Configuration

Design	WR-284 Standard Gain Horn
Pattern	Directional
Polarization	Linear
Coaxial Interface	N Female

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	2.6		3.95	GHz
<b>Waveguide Standard Gain Horn</b>				
Gain		20		dB
<b>Waveguide to Coaxial Adapter</b>				
Input VSWR		1.3:1		

### Mechanical Specifications

<b>Size</b>	
Length	33.13 in 841.5 mm
Width/Diameter	15.52 in 394.21 mm
Height	10.67 in 271.02 mm

#### RF Connector

Type	N Female
------	----------

#### Waveguide Interface

Waveguide Size	WR-284
Flange Type	CMR-284
Body Material and Plating	Aluminum

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Environmental Specifications

**Compliance Certifications** (see [product page](#) for current document)

## Plotted and Other Data


2 Dimensional OML Drawing      FM9863B/NF-20  
Notes:

WR-284 Standard Gain Horn Antenna Operating From 2.6 GHz to 3.95 GHz, 20 dBi Nominal Gain, Type N Female Input Connector, ProLine from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [WR-284 Standard Gain Horn Antenna Operating From 2.6 GHz to 3.95 GHz, 20 dBi Nominal Gain, Type N Female Input Connector, ProLine FM9863B/NF-20](#)

URL: <https://www.fairviewmicrowave.com/standard-gain-horn-0-fm9863b-nf-20-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



T-Rev.D