

2.4 GHz 15 dBi Yagi Antenna

The Fairview Microwave FM51YA1003 Radome Enclosed Yagi WiFi Antenna features high gain and a 30° beam-width. It is ideally suited for directional and multipoint IEEE 802.11b, 802.11g and 802.11n wireless LANs, Bluetooth®, public wireless hotspot applications and other systems operating in the 2.4GHz ISM band. The unique design of this antenna allows it to be installed for either vertical or horizontal polarization.

This WiFi antenna is enclosed within a UV-stable, UL flame rated radome for all-weather operation. The FM51YA1003 antenna is supplied with a 60 degree tilt and swivel mast mount kit.

Configuration

Design	Yagi
Gain	14.5 to 14.5 dBi
Polarization	Vertical or Horizontal
Cable Type	Coax Cable
Cable Length	12 in [304.8 mm]
Connector Type	N Female
Number of Ports	1
Lightning Protection	DC Short

Electrical Specifications

Description	Min	Typ	Max	Units
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		14.5		dBi
Input Power			50	Watts

Specifications by Frequency

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	2.4-2.5					GHz
Gain	14.5					dBi
Horiz. Beam Width	30					Degrees
Vert. Beam Width	30					Degrees
Max Input Power	50					Watts

Mechanical Specifications

Radome Material	Polymer
Size	
Length	18.2 in [462.28 mm]
Width	3 in [76.2 mm]
Height	3 in [76.2 mm]
Mounting Mast Diameter	1.25 to 2 in [31.75 to 50.80 mm]
Weight	0.96 lbs [435.45 g]

Mechanical Specification Notes:
Radome material is UV-inhibited Polymer.



Features:

- 12in low-loss coax lead terminated with a N-Female connector
- 30° beam-width & DC Short lightning protection
- Light weight, UV-stable & UL flame rated radome
- Includes tilt and swivel mast mount
- Can be installed for either vertical or horizontal polarization

Applications:

- 2.4 GHz ISM Band
- IEEE 802.11b, 802.11g & IEEE 802.11n Wireless LAN
- Directional and multipoint applications
- Bluetooth® & public wireless hotspot
- WiFi & wireless video systems

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Environmental Specifications

Temperature

Operating Range -20 to +60 deg C
Wind Loading 150 MPH [241.4 KPH]

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

2.4 GHz 15 dBi Yagi Antenna from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [2.4 GHz 15 dBi Yagi Antenna FM51YA1003](#)

URL: <https://www.fairviewmicrowave.com/single-antenna-14.5-dbi-gain-n-fm51ya1003-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

