

WR-137 Standard Gain Horn Antenna Operating From 5.85 GHz to 8.2 GHz, 10 dBi Nominal Gain, Type N Female Input Connector, ProLine

The Fairview Microwave FM9859B/NF-10 Proline series standard gain horn antenna (also known as waveguide horn) is part of our huge selection of waveguide antennas. This Fairview Microwave standard gain horn antenna is manufactured with a WR-137 input and a Type N waveguide to coaxial transition adapter. Our standard gain horn antenna, WR-137, has a 10 dBi nominal gain. This WR-137 standard gain horn from Fairview Microwave has a female Type N waveguide to coax transition adapter. The 10 dBi Fairview Microwave WR-137 horn antenna operates from 5.85 GHz to 8.2 GHz. Fairview Microwave's Type N female WR-137 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and rectangular input. It is part of over 40,000 RF, microwave and millimeter wave components available at Fairview Microwave. Waveguide standard gain horn antennas, such as the FM9859B/NF-10, are used in a wide variety of applications due to their high power handling capability, low loss, high directivity, and near constant electrical performance. The WR-137 FM9859B/NF-10 waveguide horn is US made and TAA compliant. Our WR-137 standard gain horn Proline antennas with Type N female interface can ship same day to anywhere in the world.

Configuration

Design WR-137 Standard Gain Horn
Pattern Directional

Polarization Linear
Coaxial Interface N Female

Electrical Specifications

| Description | Min | Тур | Max | Units |
|----------------------|-----------|-----|-------|-------|
| Frequency Range | 5.85 | | 8.2 | GHz |
| Impedance | | 50 | | Ohms |
| Waveguide Standard | Gain Horn | | | |
| Gain | | 10 | | dB |
| Waveguide to Coaxial | Adapter | | | |
| Input VSWR | | | 1.3:1 | |
| | | | | |

Mechanical Specifications Size

 Length
 4.38 in 111.25 mm

 Width/Diameter
 2.02 in 51.31 mm

 Height
 1.48 in 37.59 mm

RF Connector

Type N Female

Waveguide Interface

Waveguide Size WR-137 Flange Type CMR-137

FM9859B/NF-10 DATA SHEET



Features:

- WR-137 Rectangular Waveguide Interface
- 5.85 GHz to 8.2 GHz
- 10 dBi Nominal Gain
- Type N Female Connector

Applications:

- Antenna Measurements
- Wireless Communication
- Laboratory Use
- Microwave Radio Systems

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Environmental Specifications

Compliance Certifications (see product page for current document)

Plotted and Other Data

2 Dimensional OML Drawing Notes:

FM9859B/NF-10

WR-137 Standard Gain Horn Antenna Operating From 5.85 GHz to 8.2 GHz, 10 dBi Nominal Gain, Type N Female Input Connector, ProLine from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF ondemand.

For additional information on this product, please click the following link: WR-137 Standard Gain Horn Antenna Operating From 5.85 GHz to 8.2 GHz, 10 dBi Nominal Gain, Type N Female Input Connector, ProLine FM9859B/NF-10

URL: https://www.fairviewmicrowave.com/wr-137-waveguide-standard-gain-horn-antenna-10-db-n-fm9859b-nf-10-p. aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





