



Engineering Grade 3.5mm Female (Jack) to 2.4mm Female (Jack) Adapter with Stainless Steel Body

3.5mm female to 2.4mm female adapter part number FMAD1633 from Fairview Microwave is in-stock and ships same day. This Fairview 3.5mm to 2.4mm adapter has a female to female gender configuration and is built of durable stainless steel in a engineering grade design. FMAD1633 3.5mm female to 2.4mm female adapter operates to 26.5 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum. The 3.5mm connector mates mechanically with commercially available SMA and 2.92mm (K) connectors. The 2.4mm connector mates mechanically with commercially available 1.85mm (V) connectors.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		26.5	GHz
VSWR			1.25:1	
Operating Voltage (AC)			150	Vrms
DWV (AC)			500	Vrms
Insulation Resistance	5,000			MOhms
RF Leakage			100	dB

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 1	1 to 2	2 to 4.5	4.5 to 9	9 to 26.5	GHz
Insertion Loss, Max	0.05	0.071	0.106	0.15	0.257	dB

Mechanical Specifications

Size

Length	0.84 in [21.40 mm]
Width	0.31 in [7.90 mm]
Height	0.31 in [7.90 mm]
Weight	0.02 lbs [9.07 g]

Description	Connector 1	Connector 2
Туре	3.5mm Female	2.4mm Female
Polarity	Standard	Standard
Mating Cycles, Min	500	500
Mating Torque	7.1 to 9.7 in-lbs	7.08 to 9.74 in-lbs
	[0.80 to 1.10 Nm]	[0.80 to 1.10 Nm]
Contact Captivation Axial Force, Min	6.1 lbs [2.77 kg]	4.5 lbs [2.04 kg]
Coupling Proof Torque	15 in-lbs [1.7 Nm]	15 in-lbs [1.7 Nm]

De a

Configuration:

- 3.5mm Female Connector 1
- 2.4mm Female Connector 2
- 50 Ohm
- Engineering Grade Design
- Straight Body Geometry

Features:

- VSWR of 1.25:1 max up to 26.5 GHz
- Gold Over Nickel Plated Beryllium Copper Contact

Applications:

- Enables Between Series Connections
- General Purpose Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Coupling Retention, Min 60.7 lbs [27.53 kg] 60.7 lbs [27.53 kg]

Material Specifications

Description	Connector 1	Connector 2	
Туре	3.5mm Female	2.4mm Female	
Contact Material	Beryllium Copper	Beryllium Copper	
Contact Plating	Gold Over Nickel	Gold Over Nickel	
Insulation Material	PPO	PPO	
Body Material	Stainless Steel	Stainless Steel	
Body Plating	Passivated	Passivated	
Gasket Material	Silicone	Silicone	
Coupling Nut Material	Stainless Steel	Stainless Steel	
Coupling Nut Plating	Passivated	Passivated	

Environmental Specifications

Temperature

Operating Range Humidity Thermal Shock Salt Spray

-55 to +105 deg C MIL-STD-202, Method 206 MIL-STD-202, Method 107, Condition B

MIL-STD-202, Method 107, Condition B MIL-STD-202, Method 101, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Engineering Grade 3.5mm Female (Jack) to 2.4mm Female (Jack) Adapter with Stainless Steel Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Engineering Grade 3.5mm Female (Jack) to 2.4mm Female (Jack) Adapter with Stainless Steel Body FMAD1633

URL: https://www.fairviewmicrowave.com/engineering-grade-3.5mm-female-to-2.4mm-female-adapter-mil-std-202-method-206-with-stainless-steel-body-fmad1633-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020 REV 1 Page 2 of 3





