

## 2.15 dBi, 3.5 inch UHF Rubber Duck Antenna, 400-520 MHz, SMA Male Connector, Vertical Polarization

The FMANRBD1004 rubber duck antenna from Fairview is part of our extensive line of directional antennas that we offer with global same-day shipping from our facilities certified to ISO 9001:2015. Fairview's high-quality single-band rubber duck antenna has a 2.15 dBi nominal gain and can be procured with no order limit. This rubber duck single-band 2.15 dBi antenna has a frequency range of 400 MHz to 520 MHz.

We lead the industry in supplying products like this 400 MHz to 520 MHz single-band antenna, along with other RF, microwave, and millimeter wave components. This rubber duck antenna from Fairview uses a SMA connector and has a maximum input power of 20 watts. Use our single-band rubber duck antenna with vertical polarization for fixed and mobile services, public safety or emergency services, trunking for two-way radio communications, land and private mobile radio (LMR) (PMR), PtP or PtMP, tetra, and P-25 applications.

Fairview's rubber duck antenna with 2.15 dBi gain has a SMA-type male connector. This SMA-series male connectorized omnidirectional antenna is 0.5 inches tall, 0.5 inches wide, and 3.54 inches long. The FMANRBD1004 UHF antenna has 360-degrees of horizontal and 80-degrees of vertical HPBW. Our high-quality antenna has a maximum input VSWR (voltage standing wave ratio) of 2:1.

Fairview's 50 Ohms impedance antenna can operate at temperatures ranging from -40 °C to 60 °C. This single-band rubber duck antenna is offered with expert technical support, PDF datasheets, and CAD drawings with dimensions and specifications. Order your 2.15 dBi UHF rubber duck antennas now and enjoy our international or domestic same-day shipping.

### Configuration

Design	Rubber Duck
Gain	2.15
Polarization	Vertical
Connector Type	SMA Male

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	400		520	MHz
Input VSWR			2:1	
Impedance		50		Ohms
Gain		2.15		dBi
Horizontal (Azimuth) Beam Width		360		Degrees
Vertical (Elevation) Beam Width		80		Degrees
Input Power			20	Watts

### Mechanical Specifications

<b>Size</b>	
Length	3.54 in [89.92 mm]
Width	0.5 in [12.7 mm]
Height	0.5 in [12.7 mm]
Weight	0.022 lbs [9.98 g]



### Features:

- 400 MHz to 520 MHz, 2.15 dBi Gain
- SMA-male connector
- Heliflex whip antenna
- Plug and play
- 20W power handling
- VSWR < 2:1
- Vertical polarization

### Applications:

- PtP or PtMP applications
- Trunking for two-way radio comms
- UHF applications
- Public Safety / Emergency services
- Tetra and P-25 applications exclusively supported
- Land and Private mobile radio (LMR) (PMR)
- Fixed and mobile services

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

## Environmental Specifications

### Temperature

Operating Range -40 to +60 deg C

**Compliance Certifications** (see [product page](#) for current document)

## Plotted and Other Data

Notes:

2.15 dBi, 3.5 inch UHF Rubber Duck Antenna, 400-520 MHz, SMA Male Connector, Vertical Polarization from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [2.15 dBi, 3.5 inch UHF Rubber Duck Antenna, 400-520 MHz, SMA Male Connector, Vertical Polarization FMANRBD1004](#)

URL: <https://www.fairviewmicrowave.com/2.15-dbi-3.5-inch-uhf-rubber-duck-antenna-400-520-mhz-sma-male-connector-vertical-polarization-fmanrbd1004-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

