

FMAN51156 DATA SHEET

Whip Antenna Operates From 806 MHz to 880 MHz With a Nominal 0 dBi Gain SMA Female Input Connector IP67 Rated

Fairview Microwave's ¼ wave portable omni whip antennas feature a textured black finish and a strain-relief base to ensure durability and repeatable RF performance. Our ¼ wave portable omni whip antennas are availabile with operating frequencies as low as 400 MHz and as high as 960 MHz. These antennas are offered with gain ranges from unity to 2 dBi. The omni-directional radiation pattern and IP67 rating make these antennas ideal for mobile radio communications.

- Operating frequencies from 400 MHz to 960 MHz
- · Gain ranges from unity to 2 dBi
- VSWR less than 2:1, in most cases
- 50 Ohm Impedance
- · IP67 Rated
- Variety of connector types available (SMA Female, MX, or MD) for use in many portable handheld radio applications. See below for common brand & connector combinations.
- MX (1/4-32 x 7/32) Commonly used in: Motorola, Radius, Saber, Saber+, Spirit, Expo, Kenwood, Maxon, Midland, Wilson, GE Monogram, and Vertex Standard.
- MD (M7 x 1.0) Commonly used in: GE
- SMA Female (SF) Commonly used in: Motorola, Visar, and Kenwood

Electrical Specifications*

Description	Min	Тур	Max	Units
Frequency	806		880	MHz
Impedance		50		Ohms
Nominal Gain	0			dBi
Input VSWR			2:1	

^{*} Values at 25°C, sea level

Mechanical Specifications

Size

 Length
 3.17 in [80.52 mm]

 Width
 0.58 in [14.73 mm]

Weight 0.025 lbs [11.34 g]

Environmental Specifications

Temperature

Operating Range -20 to +65 deg C

Environment IP67

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

RoHS Compliant Yes

Plotted and Other Data

Notes:

Values at 25 °C, sea level



Features:

- Design: Whip Portable
- Frequency Range: 806 to 880 MHz
- Polarization: Vertical
- Interface 1: SMA Female
- Number of Output Ports: 1

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Whip Antenna Operates From 806 MHz to 880 MHz With a Nominal 0 dBi Gain SMA Female Input Connector IP67 Rated from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Whip Antenna Operates From 806 MHz to 880 MHz With a Nominal 0 dBi Gain SMA Female Input Connector IP67 Rated FMAN51156


The information contained in this document is accurate to the best of our knowledge and representative of the part

URL: http://www.fairviewmicrowave.com/whip-antenna-0-dbi-sma-female-fman51156-p.aspx

described	herein. It may be	necessary to m	ake modifications t	to the part and/or	the documentation of t	he part, in order
to implem	ent improvements.	Fairview Micro	wave reserves the	right to make such	changes as required.	Unless otherwise
stated, all	specifications are	nominal. Fairv	ew Microwave doe	s not make any re	presentation or warran	ty regarding the
suitability	of the part describ	ed herein for a	ny particular purpo	se, and Fairview N	licrowave does not ass	ume any liability
arising ou	t of the use of any	part or docume	ntation.			







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].				
Whip Antenna Operates From 806 MHz to 880 MHz With a Nominal 0 dBi Gain SMA Female Input Connector IP67 Rated	DWG NO FMAN51156		CAGE CODE 3FKR5		
	CAD FILE 111314	SHEET	SCAL	E N/A	SIZE A