

400 to 470 MHz, 3 dBi Folded Diploe Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR

Fairview Microwave's FMANED1014 3 dBi folded dipole antenna, with N female connector, is an economical yet high-Performance antenna designed for high-power applications. The folded dipole antenna's beamwidth can be adjusted according to applications by fixing dipoles at certain heights and directions. This high gain 3 dBi antenna transmits high-power signals, increasing the signal strength and thus providing improved coverage, better-broadcast control, and faster speed. This folded dipole antenna can output frequencies from 400 to 470 MHz, which is useful for military communications, trunking, public safety, industrial communication, and amateur radio applications.

Fairview Microwave's folded dipole antenna uses vertical polarization to transmit signals, thus reducing interference and performing better at lower heights. All components of this 3 dBi antenna are DC grounded for lightning protection, rugged outdoor design, and have a high-power handling capacity. The folded dipole antenna has 1 port to connect an external circuit with 100W maximum input power per port.

This Fairview Microwave's 400 to 470 MHz VHF/UHF antenna is one of the simplest and most widely used antenna producing radiation patterns like that of an electric dipole. FMANED1014 folded dipole antenna is a dipole standalone made of aluminum alloy, and thus packaging, transportation, and installation become easier. It has a 1.5 VSWR that results in the best power transfer and reduced losses. It comes with a threaded and weatherproof N female connector type which ensuring a reliable physical connection and can be fixed on a pole using the U-bolt brackets that come with the antenna.

FMANED1014 antenna with a 3 dBi maximum gain is ideal for LMR, military, airports, construction, mining, commercial applications, and radio users. This FMANED1014 folded dipole antenna from Fairview Microwave comes in compact packaging for lower shipping costs. Fairview Microwave's 400 to 470 MHz, 3 dBi folded dipole antenna with a N female connector is in stock and ready to ship the same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other Fairview Microwave products.

Configuration

Design Dipole
Polarization Vertical
Connector Type Number of Ports 1
Lightning Protection Dipole
Dipole
Vertical
N Female
D Female
D C Ground

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	400		470	MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain			3	dBi
Input Power			100	Watts

Mechanical Specifications

Radome Material Aluminum Alloy

FMANED1014 DATA SHEET



Features:

- Frequency coverage for 400 MHz to 470 MHz with Type N Female connector and gain 3 dBi / 0.85 dBd antennas
- Multiple Folded dipoles can be mouted on a mast for best performance
- Feild adjustable radition patterns with 100W max input power per port
- Easy and quick time to installations with U-Bolt mounts
- Industrially tuned folded dipole allows plug and play
- Weather and corrision free made of high-grade aluminum alloys
- · Vertical Polarization

Applications:

- Outdoor point-to-point (PtP) or point-to-multipoint (PtMP) applications
- UHF radio applications supported with Trunking for two-way radio communications
- Public Safety / Emergency services / Marine communications / Rail road communications
- Tetra and P-25 Applications exclusively supported
- Land Mobile Radio (LMR) and Private Mobile Radio (PMR)
- Fixed and mobile services for paging/voice/data in full duplex and half duplex mode

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Size

 Length
 12.5 in [317.5 mm]

 Width
 13.6 in [345.44 mm]

 Height
 1.3 in [33.02 mm]

 Weight
 10.56 lbs [4.79 kg]

Environmental Specifications

Temperature

Operating Range -40 to +80 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

400 to 470 MHz, 3 dBi Folded Diploe Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 400 to 470 MHz, 3 dBi Folded Diploe Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR FMANED1014

URL: https://www.fairviewmicrowave.com/dbi-antenna-400-470-mhz-n-type-connector-fmaned1014-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020

REV 1 Page 2 of 3





