

617 to 6000 MHz 4G, 5G, Wi-Fi, GPS Multiband Shark Fin Antenna, SMA Male, RP SMA Male Connectors

The FMANMOB1000 Multiband combination "shark fin" Antenna from Fairview Microwave is a high-performance omnidirectional antenna operating from 600 MHz to 6000 MHz and is available to ship same day. It is a UV stabilized, IP69K outdoor rated antenna with black paintable ABS radome. The FMANMOB1000 is ideally suited for vehicle mounted applications where Cellular, Wi-Fi, and GPS bands are needed in a single design.

The Fairview Microwave FMANMOB1000 is a mobile antenna providing broad coverage, low latency, increased network capacity and supports 2x2 MIMO (617-960MHz, 1690-6000MHz) and 3x3 MIMO (2400-2500MHz, 4900-6000MHz). This 7-port omnidirectional antenna has multiple connector types all with 13ft cable lengths. This 4G, 5G, Wi-Fi 6, GPS L1, GLONASS G1 combination omni antenna has 3 SMA Male connectors (2 Cellular, 1 GPS) and 3 RPSMA Male connectors (Wi-Fi). FMANMOB1000 also features an auxiliary antenna port with RPSMA Female connector mount with 13ft RG58 cable terminated with RPSMA Male connector. This external port will support an antennas operating from 138 MHz to 6000 MHz with RPSMA Male connector.

Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other Fairview Microwave products.

Configuration

Design	Mobile
Gain	4 dBi
Polarization	Vertical
Cable Length	157.5 in [400.05 cm]
Connector Type	SMA Male
Interface 2	SMA Male Reverse Polarity
Number of Ports	7

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	617		6,000	MHz
Input VSWR			2:1	
Impedance		50		Ohms
Noise Figure		2.7		dB
Input Power			25	Watts
Operating DC Voltage	3		5	Volts
Current		15		mA

Specifications by Frequency

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	0.617-0.96	1.69-6	2.4-2.5	4.9-6	1.562-1.612	GHz
Gain	4	6	5	6	26	dBi
VSWR	2:1	2:1	2:1	2:1	2:1	



Features:

- Aerodynamic Shark Fin Design
- 600 MHz to 6 GHz
- 2x2 MIMO Cellular, 3x3 MIMO Wi-Fi
- LNA Integrated GPS
- IP69K Rated
- 13ft pig tails
- Auxiliary External Antenna Port

Applications:

- Infotainment systems, Routers, Wi-Fi hotspots, HD video transmission, Gateways, Dash cameras, Public transportation
- Connected cars or self-driving cars, Fleet management, Logistics
- Public Safety Networks
- IoT, 4G/5G, Zigbee, Bluetooth, Wi-Fi
- GPS L1, GLONASS G1

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

GPS Specifications

Frequency Range	1562 - 1612
VSWR	<2.0:1 ± 4 MHz
LNA Gain	26 dB
Out of band rejection	>40 dB (@ > +/- 100 MHz)
Typical Noise Figure	≤ 2.7 dB
Notch Filter rejection @787MHz	24 dB
Operating Voltage	3 - 5 VDC
Typical Current	15 mA
Cable Type / Length	RG174 / 13 ft [4 m]
Connector Type	SMA Male

Mechanical Specifications

Radome Material UV Resistant ABS

Size

Length 11.22 in [284.99 mm]
 Width 3.15 in [80.01 mm]
 Height 4.33 in [109.98 mm]
 Weight 3 lbs [1.36 kg]
 Color Black

Environmental Specifications

Temperature

Operating Range -40 to +85 deg C

Humidity 5 to 95
 Ingress Protection IP69K

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

617 to 6000 MHz 4G, 5G, Wi-Fi, GPS Multiband Shark Fin Antenna, SMA Male, RP SMA Male Connectors from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [617 to 6000 MHz 4G, 5G, Wi-Fi, GPS Multiband Shark Fin Antenna, SMA Male, RP SMA Male Connectors FMANMOB1000](#)

URL:

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

