

423 to 443 MHz, 8 dBi Collinear Omnidirectional Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR

Fairview Microwave's FMANOM1051 4.5 dBi omnidirectional antenna, with N female connector, is an economical yet high-Performance antenna designed for high-power applications. This high gain 4.5 dBi antenna transmits high-power signals, increasing the signal strength and thus providing improved coverage, better-broadcast control, and faster speed. This omnidirectional antenna can output frequencies from 423 to 443 MHz, which is useful for military communications, trunking, public safety, industrial communication, and amateur radio applications.

This omnidirectional antenna from Fairview Microwave FMANOM1051 uses vertical polarization to transmit signals, thus reducing interference and performing better at lower heights. All components of this 4.5 dBi antenna are DC grounded for lightning protection, rugged outdoor design, and have a high-power handling capacity. The omnidirectional antenna has 1 port to connect an external circuit with 100W maximum input power per port.

Fairview Microwave's FMANOM1051 omnidirectional antenna is made of fiberglass, is omnidirectional, and covers good bandwidth and range. It has a 1.5 VSWR that results in the best power transfer and reduced losses. These 423 to 443 MHz VHF/UHF antennae radiates equal power in all directions perpendicular to the axis, with power declining to zero on the axis, when graphed, the radiation pattern describes a doughnut shape. It comes with a N female connector, which is threaded and weatherproof that ensuring a reliable physical connection.

This Fairview Microwave's FMANOM1051 with a 4.5 dBi maximum gain is ideal for LMR, military, airports, construction, mining, commercial applications, and radio users. This FMANOM1051 omnidirectional antenna from Fairview Microwave comes in compact packaging for lower shipping costs. Fairview Microwave's 423 to 443 MHz, 4.5 dBi omnidirectional antenna with a N female connector is in stock and ready to ship the same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other Fairview Microwave products.

Configuration

Design Omni
Polarization Vertical
Connector Type Number of Ports 1
Lightning Protection DC Ground

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	423		443	MHz
Input VSWR			1.5:1	
Impedance		50		Ohms
Gain			8	dBi
Input Power			100	Watts

Mechanical Specifications

Radome Material Fiberglass

Size

Length 2.5 in [63.5 mm]

FMANOM1051 DATA SHEET



Features:

- Frequency coverage for 423 MHz to 443 MHz with Type N Female connector
- Moderate Gain 8 dBi / 5.85 dBd antennas
- Easy and quick time to installations
- Industrially tuned antenna allows plug and play
- Environmentally friendly strong fiberglass radome material
- Direct ground lightning proctection
- 100 W max input power per port
- Vertical Polarization

Applications:

- Outdoor point-to-point (PtP) or point-to-multipoint (PtMP) applications
- UHF radio applications supported with Trunking for two-way radio communications
- Public Safety / Emergency services / Marine communications / Rail road communications
- Tetra and P-25 Applications exclusively supported
- Land Mobile Radio (LMR) and Private Mobile Radio (PMR)
- Fixed and mobile services for paging/voice/data in full duplex and half duplex mode

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





 Width
 1.2 in [30.48 mm]

 Height
 1.2 in [30.48 mm]

 Weight
 6.6 lbs [2.99 kg]

Environmental Specifications Temperature

Operating Range -40 to +80 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

423 to 443 MHz, 8 dBi Collinear Omnidirectional Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 423 to 443 MHz, 8 dBi Collinear Omnidirectional Antenna with N Female, Vertical Polarization, 1 Port, 1.5 VSWR FMANOM1051

URL: https://www.fairviewmicrowave.com/dbi-antenna-423-443-mhz-n-type-connector-fmanom1051-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2020 REV 1 Page 2 of 3





