

## FMCN0011 DATA SHEET

# RA 75 Ohm 12G SDI BNC Female Bulkhead PCB Connector Thru Hole Solder Attachment

75 Ohm RA BNC female bulkhead connector with solder attachment for thru hole PCB, part number FMCN0011, from Fairview Microwave is in-stock and ships same day. This BNC female connector operates up to a maximum frequency of 12 GHz. Its right angle body geometry facilitates connections in tight spaces. Fairview's FMCN0011 bulkhead BNC connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications. Fairview Microwave's 12G-SDI BNC connector FMCN0011 utilizes 12Gb/s data transfer rates to enable high resolution uncompressed video signal transmission. These products offer 4K and Ultra-HD quality signals that meet SMPTE Standard 2082-1. These 75 Ohm connectors are available in PCB edge-mount, straight, or right angle configurations, as well as coaxial connectors to be used in industry standard cable assemblies.

Fairview's 75 ohm BNC female bulkhead connector FMCN0011 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

## **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		12	GHz

#### **Mechanical Specifications**

**Size** Length Width/Dia. Height Weight

1.3 in [33.02 mm] 0.83 in [21.08 mm] 0.63 in [16 mm] 0.05 lbs [22.68 g]

#### **Material Specifications**

Description	Material	Plating	
Contact	Brass	Gold 10 µin minimum	
Insulation	PTFE		
Outer Conductor	Brass	Nickel 100 µin minimum	
Body	Brass	Nickel 100 µin minimum	
Washer	Brass	Nickel 100 µin minimum	



## **Configuration:**

- BNC Female Connector
- 75 Ohms
- Right Angle Body Geometry
- Thru Hole Interface Type
- Solder Attachment
- Bulkhead

#### Features:

- Operating Frequency of 12 GHz Max.
- Gold Plated Brass Contact
- 10 µin minimum contact plating
- Meets SMPTE ST 2082-1
- Backwards Compatible with 2081-1
- 12Gb/s Transmission
- Cost Effective

## **Applications:**

- General Purpose Test
- Rack and Panel Mount Applications
- PCB Applications
- CATV
- 12G-SDI, Video, and Broadband UHDTV
- Broadband Internet Delivery
- Broadcast A/V
- 4K/8K Video Equipment
- Medical Equipment Requiring

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

RA 75 Ohm 12G SDI BNC Female Bulkhead PCB Connector Thru Hole Solder Attachment from Fairview Microwave is instock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: RA 75 Ohm 12G SDI BNC Female Bulkhead PCB Connector Thru Hole Solder Attachment FMCN0011

URL: https://www.fairviewmicrowave.com/bnc-female-pcb-connector-fmcn0011-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





