

FMHR0001 DATA SHEET

BNC Male to BNC Male MIL-DTL-17 Cable M17/60-RG142 Coax

MIL-DTL-17 BNC (M39012/16-0014) to BNC (M39012/16-0014) cable assemblies with test reports from Fairview Microwave are part of our full line of reliable RF components available with same-day shipping. These COTS (commercial-off-the-shelf) cable assemblies using M17/60-RG142 have traceable processes and materials that are recorded and provided in the included test report. The MIL-DTL-17 coaxial cable and MIL-PRF-39012 connectors are assembled with J-STD-001 soldering processes and meet WHMA-A-620 workmanship criteria. These carefully selected materials, assembly processes and test sequence ensure a dependable cable assembly for high reliability applications where the cost of failure or replacement is high. Each serialized BNC to BNC MIL-DTL-17 cable assembly is traceable to its component lots and test data ship with every cable.

This MIL-C-17 M39012/16-0014 to M39012/16-0014 cable assembly using M17/60-RG142 datasheet PDF contains specifications, CAD drawing and dimensions that are shown below. Fairview Microwave offers these high reliability RF cable assemblies with test data, and many other RF, microwave and millimeter wave components which allow designers to configure and customize their signal systems however they like. Whether the need is to provide reliable MIL-DTL-17 interconnects or supporting test reports, Fairview Microwave has the right cable assemblies for the job. Fairview can also expertly build your custom cable assemblies for you and ship same day.

Referenced Specifications

IPC/WHMA-A-620	Requirements and Acceptance for Cable and Wire Harness Assemblies
MIL-DTL-17	Cables, Radio Frequency, Flexible and Semirigid, General Specification for
MIL-STD-348	Radio Frequency Connector Interfaces for MIL- DTL-3643, MIL-DTL-3650, MIL-DTL-3655, MIL- DTL-25516, MIL-PRF-31031, MIL-PRF-39012, MIL-PRF-49142, MIL-PRF
MIL-PRF-39012	Connectors, Coaxial, Radio Frequency, General Specification for
IPC J-STD-001	Requirements for Soldered Electrical and Electronic Assemblies
IPC J-STD-006	Requirements for Electronic Grade Solder Alloys and
	Fluxed and Non-Fluxed Solid Solders for Electronic Soldering Applications
SAE AS5942	Marking of Electrical Insulating Materials
SAE AS23053	Insulation Sleeving, Electrical, Heat Shrinkable, General Specifications For
SAE AS22520	Crimping Tools, Wire Termination, General Specification For

Material Specifications

Component	Specification
Cable	M17/60-RG142 in accordance with MIL-DTL-17
Connector 1	M39012/16-0014 in accordance with MIL-PRF-39012
Connector 2	M39012/16-0014 in accordance with MIL-PRF-39012
Heat Shrink 1	M23053/5-106-0 in accordance with SAE AS23053
Heat Shrink 2	M23053/5-106-0 in accordance with SAE AS23053



Configuration:

- Connector 1: M39012/16-0014(BNC Male)
- Connector 2: M39012/16-0014(BNC Male)
- Cable: M17/60-RG142

Features:

- Max Frequency 4 GHz
- 69.5% Phase Velocity
- Double Shielded
- FEP Jacket
- J-STD-Soldering
- Lot Traceability Data
- Qualified cable and connectors (QPL)
- Acceptance Test Report
- RF Test Data
- In stock and ready to ship

Applications:

- Hi-Reliability
- Unmanned Systems
- Drones
- MIL-DTL-17 Requirements
- Military Electronics

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Solder

SN63 in accordance with J-STD-006

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		4	GHz
VSWR			1.6:1	
Velocity of Propagation		69.5		%
Capacitance	2	9.3 [96.1	3]	pF/ft [pF/m]
Dielectric Withstanding Voltage (AC)			1,500	Vrms

Specifications by Frequency						
Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.4	1	3	4	GHz
Insertion Loss (Max) 0.044	0.093	0.153	0.293	0.35	dB/ft
	0.14	0.31	0.5	0.96	1.15	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Cable Outer Diameter 0.19 0.195 0.2 in	Description	Min	Тур	Max	Units
	Cable Outer Diameter	0.19	0.195	0.2	in
Weight 0.14 [63.5] Ibs [g]	Weight			0.14 [63.5]	lbs [g]

Cable Characteristics

Component	Specification		
Cable Type	M17/60-RG142		
Impedance	50 Ohms		
Inner Conductor Type	Solid		
Inner Conductor Mat. & Plat.	Copper Clad Steel, Silver		
Dielectric Type	PTFE		
Number of Shields	2		
Shield Layer 1	Silver Clad Copper		
Shield Layer 2	Silver Clad Copper		
Outer Conductor Diameter	0.171 in [4.34 mm]		
Jacket Material	FEP		





Connector Characteristics

Description	Connector 1	Connector 2	
Туре	BNC Male	BNC Male	
Specification	MIL-PRF-39012	MIL-PRF-39012	
Impedance	50 Ohms	50 Ohms	
Contact Mat. & Plat.	Brass, Gold	Brass, Gold	
Contact Plating Spec.	MIL-G-45204	MIL-G-45204	
Dielectric Type	Teflon	Teflon	
Body Mat. & Plat.	Brass, Silver	Brass, Silver	
Body Plating Spec.	QQ-S-365	QQ-S-365	
Seal Gasket Material	Silicone Rubber	Silicone Rubber	
Contact Gage Spec.	0.210 to 0.230 in	0.210 to 0.230 in	
Insulator Gage Spec.	0.208 to 0.228 in	0.208 to 0.228 in	

Mechanical Specification Notes:

Environmental Specifications

Description		Sp	ecification	
Temperature Operating Rar	nge	-55	to +165 deg C	
Temperature Operating Rar	nge	-55	to +165 deg C	

Compliance Certifications (see product page for current document)

Process Specifications

Process	Specification
Soldering	in accordance with J-STD-001, class 3
Crimping	dies in accordance with SAE AS22520
Marking	shall meet the adherence requirements of SAE AS5942
Workmanship	shall be in accordance with IPC/WHMA-A-620, class 3

Tests and Inspections

Test	Sampling	
Connector Gaging (pin and insulator position)	100%	
Insertion Loss	100%	
VSWR	100%	
Dielectric Withstanding Voltage (DWV)	100%	
Visual - workmanship, configuration and marking	100%	
Length	C=0, 1.5 AQL	
Mass	C=0, 1.5 AQL	

Plotted and Other Data

Notes:

• Values at 25°C, sea level.





How to Order

Part Number Configuration:

FMHR0001 - xx



Example: FMHR0001-12 = 12 inches long cable FMHR0001-100cm = 100 cm long cable

Cable Assembly Length Tolerances:

	Imperial	Engli <mark>sh</mark>				Me	tric	
	"L" ≤ 1 ft	+0.5	in / -0 in	"L	." ≤ 0.:	3 m	+12.5 mm / -(0 mm
1	ft < "L" ≤ 5 ft	+1 ir	n / -0 in	0.3 m	< "L"	≤ 1.5 m	+25 mm / -0	mm
5	ft < "L" ≤ 10 ft	+2 ir	n / -0 in	1.5 m	ר < "L'	'≤3 m	+50 mm / -0	mm
10) ft < "L" ≤ 25 ft	+3 ir	n / -0 in	3 m •	< "L" ≤	≤ 7.5 m	+75 mm / -0	mm
	25 ft < "L"	+2%"L	" / -0%"L"	7.	5 m <	"L"	+2%"L" / -0%	%"L"

* Cable Length = "L"

BNC Male to BNC Male MIL-DTL-17 Cable M17/60-RG142 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: BNC Male to BNC Male MIL-DTL-17 Cable M17/60-RG142 Coax

URL: https://www.fairviewmicrowave.com/bnc-male-bnc-male-cable-m17-60-rg142-coax-fmhr0001-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





