

4.3-10 Male (Plug) Termination (Load) 5 Watts,
DC to 6 GHz, Black Anodized Aluminum



FMTR1181

Features

- DC to 6 GHz Frequency Range
- 50 Ohm Impedance
- 4.3-10 Male Coaxial Interface
- Max VSWR 1.25:1
- Max Power 5 Watts (CW)

Applications

- 5G Cellular Bands
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communication
- DAS Systems

Description

Fairview Microwave's FMTR1181 is an RF termination (also called RF load or dummy load) that operates from DC to 6 GHz and handles up to 5 Watt (CW). Our 4.3-10 termination / load has a male gender. FMTR1181 4.3-10 load termination offers 1.25:1 max VSWR.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By using a terminator on an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, circulators, and switches. They are also widely used in measurement systems to ensure accurate results. Pasternack offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watt (CW).

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|------------------|---------|---------|---------|-------|
| Frequency Range | DC | | 6 | GHz |
| Impedance | | 50 | | Ohms |
| VSWR, Input | | | 1.25:1 | |
| Input Power (CW) | | | 5 | Watts |

Mechanical Specifications

Size

| | |
|--------------|---------------------|
| Length | 1.484 in [37.69 mm] |
| Width | 0.787 in [19.99 mm] |
| Height | 0.787 in [19.99 mm] |
| Weight | 0.0992 lbs [45 g] |
| Package Type | Connectorized |

Configuration

| | |
|-----------|-------------|
| Connector | 4.3-10 Male |
|-----------|-------------|

Material Specifications

| Description | Material | Plating |
|------------------|-------------------------|-----------|
| Connector 1 Body | Brass | Tri-Metal |
| Housing | Black Anodized Aluminum | |

4.3-10 Male (Plug) Termination (Load) 5 Watts,
DC to 6 GHz, Black Anodized Aluminum



FMTR1181

Environmental Specifications

Temperature

Operating Range

-40 to +75 deg C

Ingress Protection (IP) Rating

IP65

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

4.3-10 Male (Plug) Termination (Load) 5 Watts, DC to 6 GHz, Black Anodized Aluminum from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [4.3-10 Male \(Plug\) Termination \(Load\) 5 Watts, DC to 6 GHz, Black Anodized Aluminum FMTR1181](#)

URL: <https://www.fairviewmicrowave.com/rf-load-5-watts-6-ghz-4.3-10-male-fmtr1181-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMTR1181 CAD Drawing

4.3-10 Male (Plug) Termination (Load) 5 Watts, DC to 6 GHz, Black Anodized Aluminum

