

**Type N F/F In/Out Bulkhead Coaxial RF Surge Protector, DC - 3GHz, DC Pass, 40W, IP67, 40kA, Gas Discharge Tube**

RF surge protector (also known as lightning arrester) FMSP1039 from Fairview Microwave utilizing a proprietary gas tube surge protection technology protects critical hardware from lightening events while maintaining the RF performance. This RF surge protector component is manufactured in a coaxial in-line design with wide operating frequency range. All Fairview Microwave RF surge protector products are available in stock with same day shipping.



**Electrical Specifications**

Description	Surge Protector Type			Units
	Min	Typ	Max	
Frequency Range	DC		3	GHz
Impedance		50		Ohms
VSWR			1.2:1	
Return Loss			26	dB
Insertion Loss			0.26	dB
Input Power, CW 40W @ 30MHz			40	Watts
Surge Current IEC 61000-4-5 8/20µs WAVEFORM			40	kA
Turn On Voltage		150 ±20 %		Volts
Throughput Energy 8/20µsec 4kA SURGE PULSE			500	µJ

**Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 1	1 to 3				GHz
VSWR, Typ	1.1:1	1.2:1				
IL, Max	0.1	0.25				dB

**Mechanical Specifications**

**Configuration**

Input Connector N Female  
Output Connector N Female

**Environmental Specifications**

**Temperature**

Operating Range -55 to 85 deg C

Ingress Protection (IP) Rating IP 67

**Features:**

- Surge current of 40kA
- Max Power 40W(RMS)
- Frequency range from DC to 3GHz
- N-type female connectors
- Waterproof IP67 rated
- DC Pass
- VSWR <1.2
- CE & RoHS compliant
- Bi-Directional

**Applications:**

- WiFi
- GPS
- Land mobile radio

Fairview Microwave  
301 Leora Ln., Suite 100  
Lewisville, TX 75056  
Tel: 1-800-715-4396 / (972) 649-6678  
Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**


Notes:

Type N F/F In/Out Bulkhead Coaxial RF Surge Protector, DC - 3GHz, DC Pass, 40W, IP67, 40kA, Gas Discharge Tube from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Type N F/F In/Out Bulkhead Coaxial RF Surge Protector, DC - 3GHz, DC Pass, 40W, IP67, 40kA, Gas Discharge Tube FMSP1039](#)

URL: <https://www.fairviewmicrowave.com/type-n-surge-protector-3ghz-3ghz-gas-discharge-tube-fmsp1039-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.01
.XXX	±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

**NOTES:**

HARDWARE INCLUDED.

**REGULATORY COMPLIANCE:**

CE2011/65/EU(RoHS DIRECTIVE)

<p><b>Fairview Microwave</b>          RF COMPONENTS ON DEMAND. <i>Done!</i></p>	<p>NOTES:          1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.          2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.          3. DIMENSIONS ARE IN INCHES [mm].</p>					
	<p>TITLE          Type N F/F In/Out Bulkhead Coaxial RF Surge Protector, DC - 3GHz, DC Pass, 40W, IP67, 40kA, Gas Discharge Tube</p>			<p>DWG NO  <b>FMSP1039</b></p>		<p>CAGE CODE  <b>3FKR5</b></p>
	<p>CAD FILE          3/2/18</p>	<p>SHEET          1 OF 1</p>	<p>SCALE          N/A</p>	<p>SIZE          A</p>	<p>XXXX</p>	