

## N-type Female (Jack) Termination (Load) 200 Watts, 0.4 GHz to 6 GHz, Low PIM Black Anodized Aluminum

Fairview Microwave's FMTR1154 is a high power RF cable termination (also called RF load or dummy load) that operates from 400 to 6,000 MHz and handles up to 200 Watts (CW). Our N termination / load is a 50 Ohm impedance and has a female gender. FMTR1154 load termination offers 1.25:1 VSWR and low PIM (passive intermodulation) of -168 dBc typical. This Fairview Microwave 200 Watts terminator has a heatsink body which is designed to provide adequate heat dissipation within its full frequency of operation.

RF load / terminations are indispensable components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can potentially damage the device or reduce the signal integrity. By terminating an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These termination components are commonly used to terminate devices such as couplers, hybrids, and combiners. They are also widely used in measurement systems to ensure accurate results. Fairview Microwave offers a huge selection of RF, microwave and millimeter wave terminations up to 65 GHz with excellent performance over the entire operating range and power handling capabilities up to 800 Watts (CW).

### Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	0.4		6	GHz
Impedance		50		Ohms
VSWR		1.25:1		
Passive Intermodulation 2x43dBm		-168	-160	dBc
Input Power (CW)			200	Watts
Input Power (Peak) 8% duty cycle, 20us PW			2	kWatts

### Mechanical Specifications

Size	
Length	6.69 in [169.93 mm]
Width	5.12 in [130.05 mm]
Height	3.15 in [80.01 mm]
Weight	4.41 lbs [2 kg]
Package Type	Connectorized

### Configuration

Connector	N Female
Termination Design	RF Load



### Features:

- 50 Ohm Impedance
- 400 to 6,000 MHz Frequency Range
- VSWR 1.25:1
- Max Power 200 Watts (CW)
- PIM rating -168dBc Typical
- N Female Coaxial Interface

### Applications:

- Wireless
- SatCom
- Test and Measurement
- Commercial and Military Communication
- Base Station
- 4G/AWS/PCS

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

**Material Specifications**

Description	Material	Plating
Connector 1 Contact	Beryllium Copper	Gold
Body	Brass	Tri-Metal
Housing	Black Anodized Aluminum Heatsink	

**Environmental Specifications**

**Temperature**

Operating Range -40 to +75 deg C  
 Storage Range -50 to +85 deg C

Humidity <95%  
 Shock IEC 60068-2-27  
 Vibration IEC 60068-2-6-Fc  
 Altitude <5000m  
 Thermal Shock IEC 60068 -2-14-Na

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

N-type Female (Jack) Termination (Load) 200 Watts, 0.4 GHz to 6 GHz, Low PIM Black Anodized Aluminum from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [N-type Female \(Jack\) Termination \(Load\) 200 Watts, 0.4 GHz to 6 GHz, Low PIM Black Anodized Aluminum FMTR1154](#)

URL: <https://www.fairviewmicrowave.com/rf-load-200-watts-6-ghz-low-pim-n-female-fmtr1154-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

