

SMA/M/RA-SMA/M/RA FLEXIBLE CABLES LMR240 6GHZ

SCB15812-XX

SPECIFICATIONS


CABLE ASSEMBLY:
VSWR: <1.2 TYPICAL @ 6GHZ

RAW CABLE: LMR240
LOSS (EXCLUDING CONNECTORS)
@ 1GHZ: 0.08 DB/FT
@ 2GHZ: 0.47 DB/FT
@ 3GHZ: 0.68 DB/FT


OVERALL DIAMETER: .240"

CONNECTORS:
SMA: NICKEL PLATED BRASS
INTERFACE: MIL-STD-348A
CONTACTS; BRASS Au PLATTING

TORQUE 5 IN-IBS



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE

FAIRVIEW, TX WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M/RA-SMA/M/RA FLEXIBLE CABLES LMR240 6GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15812-XX	A
SCALE		SHEET	