

2 WAY POWER DIVIDER N 700-2700MHZ

MP8749-2

SPECIFICATIONS


ELECTRICAL

FREQUENCY: 700-2700 MHZ
 ISOLATION: 18 DB TYP
 POWER: 10 W AVG
 IMPEDANCE: 50 OHMS
 VSWR: 1.30:1 OUT, 1.35:1 IN
 LOSS: 3.8 DB (3+.8)


MECHANICAL

MATERIALS BODY: PASSIVATED ALUMINUM
 CONNECTORS: N-FEMALE, NICKEL PLATED BRASS
 CONTACTS: Au PLATED BeCu
 INTERFACE: MIL-STD-348A
 TEMPERATURE RANGE: -20° to +70°C

ROHS COMPLIANT



MEASUREMENTS BELOW ARE TYPICAL



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

**2 WAY POWER DIVIDER N
 700-2700MHZ**

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	MP8749-2	A
SCALE	SHEET		