

# 20 dB Fixed Attenuator SMA Female To SMA Female Up To 18 GHz Rated To 25 Watts With Black Aluminum Heatsink Body

## **Electrical Specifications\***

Description	Min	Тур	Max	Units
Frequency Range	DC		18	GHz
Impedance		50		Ohms
Attenuation Value	20 to 20			dB
Input Power			25	Watts
Peak Power			500	Watts
VSWR			1.6:1	

<sup>\*</sup> Values at 25°C, sea level

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	DC to 6	6 to 12.4	12.4 to 18	8		GHz
Insertion Loss	20					dB
VSWR	1.3:1	1.45:1	1.6:1			
Atten. Accuracy	± 0.5	± 0.75	± 1.25			dB
Max. Input Power	25					Watts

#### **Mechanical Specifications**

## **Temperature**

Operating Range -55 to +125 deg C

**Size** Lenat

Length Width Weight 4.5 in [114.3 mm] 2.41 in [61.21 mm] 0.8 lbs [362.87 g]

#### **Connectors**

Connector 1	Connector 2			
SMA Female	SMA Female			
Beryllium Copper, Gold	Beryllium Copper, Gold			
Gold				
iting	Stainless Steel, Passivated			
Stainless Steel, Passivated				
Stainless Steel				
11/16 ln.	11/16 ln.			
Stainless Steel, Passivated	Stainless Steel, Passivated			
Passivated				
	SMA Female Beryllium Copper, Gold Gold ting Stainless Steel, Passivated Stainless Steel 11/16 In. Stainless Steel, Passivated			

# SA18SFSF25W-20 DATA SHEET



## **Features:**

- Design: Fixed, Bidirectional Attenuator
- Connector 1: SMA Female
- Connector 2: SMA Female
- Body Material and Plating: Black Anodized Aluminum Heatsink

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





**Compliance Certifications** (visit www.FairviewMicrowave.com for current document)

#### **Plotted and Other Data**

Notes:

· Values at 25 °C, sea level

20 dB Fixed Attenuator SMA Female To SMA Female Up To 18 GHz Rated To 25 Watts With Black Aluminum Heatsink Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-theshelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 20 dB Fixed Attenuator SMA Female To SMA Female Up To 18 GHz Rated To 25 Watts With Black Aluminum Heatsink Body SA18SFSF25W-20

URL: http://www.fairviewmicrowave.com/20db-fixed-attenuator-sma-female-sma-female-25-watts-sa18sfsf25w-20-p. aspx

> The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



# SA18SFSF25W-20 DATA SHEET

Add to end of part number				
- yy =	Attenuation			
- 03	3 dB			
- 06	6 dB			
- 10	10 dB			
- 20	20 dB			
- 30	30 dB			
- 40	40 dB			
- 50	50 dB			
- 60	60 dB			

Part Number Configuration					
Part Number	Input Connector	Output Connector			
SA18SMSF25W	SMA Male	SMA Female			
SA18SFSF25W	SMA Female	SMA Female			
SA18NMNF25W	N Male	N Female			
SA18NFNF25W	N Female	N Female			
SA18TMTF25W	TNC Male	TNC Female			
SA18TFTF25W	TNC Female	TNC Female			
SA75DMDF25W	7/16 Ma <b>l</b> e	7/16 Female			
SA75DFDF25W	7/16 Female	7/16 Female			





Table of Information			
Connector Type	DIM "A" (REF.)		
SMA Male	0.7800		
SMA Female	0.6300		
TNC Male	0.9600		
TNC Female	1.0600		
N Female	1.0900		
N Male	1.1300		
7/16 Male	1.2800		
7/16 Female	1.3200		



FAIRVIEW MICROWAVE INC.  ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].						
20 dB Fixed Attenuator SMA Female To SMA Female Up To 18 GHz Rated To 25 Watts With Black Aluminum Heatsink Body	SA18XXXX25w-yy				CAGE CODE 3FKR5		
	CAD FILE	063014	SHEET	SCAL	E N/A	SIZE A	2233