

BNC/M - BNC/M FLEXIBLE CABLES 1GHZ RG58

SCB15030-XX


SPECIFICATIONS

CABLE ASSEMBLY:
VSWR: 1.2:1 @ < 1GHZ TYPICAL


RAW CABLE: RG58
TYPICAL LOSS (EXCLUDING CONNECTORS)
@1GHZ: 0.15 DB/FT
@2GHZ: 0.22 DB/FT
@3GHZ: 0.28DB/FT
OUTER SHIELD DIAMETER: .195"

CONNECTORS:
BNC: BRASS Au
CONTACTS Au PLATING
INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C



MEASUREMENTS BELOW ARE TYPICAL 12in CABLE



ALL DIMENSIONS IN inches(MM) Typical

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

BNC/M - BNC/M FLEXIBLE CABLES 1GHZ RG58

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SCB15030-XX	--
SCALE		SHEET	