



## **TNC Male to BNC Female Adapter**

TNC male to BNC female adapter part number SM3552 from Fairview Microwave is in-stock and ships same day. This Fairview TNC to BNC adapter has a male to female gender configuration. SM3552 TNC male to BNC female adapter operates to 4 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

## **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		4	GHz
VSWR			1.25:1	
Operating Voltage (AC)			500	Vrms
DWV (AC)			1,500	Vrms
Insulation Resistance	5,000			MOhms

**Electrical Specification Notes:** 

Values at 25° C, sea level.

#### **Mechanical Specifications**

Size	
Length	
Width	
Weight	

1.69 in [42.93 mm] 0.62 in [15.75 mm] 0.07099 lbs [32.2 g]

Description	Connector 1	Connector 2		
Туре	TNC Male	BNC Female		
Polarity	Standard	Standard		
Interface Specification	MIL-STD-348	MIL-STD-348		
Hex Size	9/16 inch			



# **Configuration:**

- TNC Male Connector 1
- BNC Female Connector 2
- 50 Ohms
- Straight Body Geometry

#### **Features:**

- VSWR of 1.25:1 max up to 4 GHz
- TNC interface meets MIL-STD-348
- BNC interface meets MIL-STD-348
- Contact plating according to MIL-G-45204
- · Gold Plated Contact

## **Applications:**

- Enables Between Series Connections
- General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





### **Material Specifications**

Description	Connector 1	Connector 2			
Туре	TNC Male	BNC Female			
Contact Plating	Gold	Gold			
Contact Plating Spec.	MIL-G-45204	MIL-G-45204			
Outer Contact Material		Brass			
Outer Contact Plating		Nickel			
Outer Conductor Contact Spec.		QQ-N-290			
Body Material	Passivated Stainless Steel				
Coupling Nut Material	Passivated Stainless Steel				

## **Environmental Specifications**

Temperature

Operating Range


-65 to +165 deg C

**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:

### **Typical Performance Data**







TNC Male to BNC Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF ondemand.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order


For additional information on this product, please click the following link: TNC Male to BNC Female Adapter SM3552

URL: https://www.fairviewmicrowave.com/tnc-male-bnc-female-adapter-sm3552-p.aspx

	ient improvemen										
	l specifications a										
suitability	of the part desc	ribed herein	for any	/ particular	purpose,	and Fair	view Mi	crowave	does not	assume a	ny liability
arising ou	t of the use of ar	ny part or do	cument	ation.							







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
TNC Male to BNC Female Adapter	DWG NO CAGE CODE SM3552 SFKR			FKR5		
	CAD FILE 071415	SHEET	SCALE	N/A	SIZE A	5568